



U.H.F. 2

# THE MAGIC CIRCLE

**U.H.F. INDOOR AERIAL FOR CHANNELS 23-34  
FOR 625 LINE TELEVISION RECEPTION**

Never before has so much performance been built into such a small space.

## LOOK AT THESE FEATURES:

- Suitable for channel 34 *now* in operation, as well as for *all* future U.H.F. channels planned for LONDON and surrounding area.
- Designed for U.H.F. only — therefore gives **PEAK PERFORMANCE**.
- Does not interfere with normal 405 line reception.
- Special directional properties ensures crystal clear reception.
- Beautifully styled in black and silver colouring.
- Supplied complete with lead and plug.
- Anti-scratch base.
- **PRICE 35/-.**

**Latimer U.H.F. AERIALS**

# ***Labgear***

## **MAGIC CIRCLE AERIAL TYPE U.H.F.2**

### **HOW TO USE LABGEAR "MAGIC CIRCLE"**

The Labgear Magic Circle Aerial will function satisfactorily in any area where U.H.F. reception with a room aerial is possible. It is impracticable to give a maximum range because of the screening effect of hills, buildings, etc. Nevertheless excellent reception has been achieved with this model at ranges in excess of 10 miles from the transmitter.

- 1 Slide the aerial out of its container and position on or near the T.V. receiver.
- 2 Plug the connector at the end of the lead into the U.H.F. aerial socket at the back of the receiver.
- 3 Switch the set for 625 line reception (make sure that your set is suitable—consult your Dealer if in doubt).
- 4 Carefully position the aerial for best reception. The position may be quite critical and it will be necessary to twist the aerial around as well as moving it from side to side.
- 5 Leave your existing T.V. Aerial for 405 line reception connected normally. The aeriels are switched automatically when you switch programmes.

**LABGEAR LIMITED, CAMBRIDGE, ENGLAND**  
**Telephone 47301 — Telegrams Labgear, Cambridge**